



Copenhagen LED Small

BRS443 GRN59-3S/740 II O-DK CLO-DDF6 C10

Little Copenhagen LED side entry, LED GreenLine 5900 lm, 740 neutral white, Safety class II, Distribution wet road (DK), Constant light output and DynaDimmer fixed presets version 6, Cable 10 m without plug

Copenhagen LED was co-designed together with Copenhagen's Office of City Architecture in order to enhance the aesthetic appeal of the city's lighting. The luminaire's timeless design comes in two sizes – mini and large – to ensure that the dimensions of the luminaire and pole are well balanced, and that the installation blends in harmoniously with its surroundings. A variety of suspensions are available, offering maximum freedom in the overall design of the installation. A choice of symmetrical or asymmetrical distributions and state-of-the-art LED technology complete the specification of an extremely adaptable luminaire.

Product data

General Information			
Lamp family code	GRN59 [LED GreenLine 5900 lm]	B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Light source replaceable	Yes		
Number of gear units	1 unit		
Driver included	Yes		
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example		
		Light source engine type	LED
		Product family code	BRS443 [Little Copenhagen LED side entry]
		Lighting Technology	LED
		Embedded control	Constant light output and DynaDimmer fixed presets version 6

Copenhagen LED Small

CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0
Luminous Flux	4,960 lumen
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	104 lm/W
Color rendering index (CRI)	≥70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution wet road (DK)

Operating and Electrical

Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	41 W
Average CLO power consumption	46 W
End CLO power consumption	51 W
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	51 W
Power Factor (Fraction)	0.9
Connection	-
Cable	Cable 10 m without plug
Number of products on MCB of 16 A type 8 B	

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit with DynaDimmer and constant light output (integrated)
Control interface	-
Constant light output	Yes

Mechanical and Housing

Reflector material	-
--------------------	---

Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Opal
Mounting device	Side-entry for diameter 48 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall height	312 mm
Overall diameter	380 mm
Effective projected area	0.08 m²

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.382, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Full product code	871829108162300
Order product name	BRS443 GRN59-3S/740 II O-DK CLO-DDF6 C10
Order code	919008632007
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	919008632007
Full product name	BRS443 GRN59-3S/740 II O-DK CLO-DDF6 C10
EAN/UPC - Case	8718291081623
EAN/UPC - Product/Case	8718291081623

Copenhagen LED Small

Dimensional drawing

