



Copenhagen LED Small

BRS443 GRN39-3S/740 II DK GR CLO-DDF6

Little Copenhagen LED side entry, LED GreenLine 3900 lm, 740 neutral white, Safety class II, Distribution wet road (DK), Flat glass, Constant light output and DynaDimmer fixed presets version 6

Copenhagen LED was co-designed together with Copenhagen's Office of City Architecture in order to enhance the aesthetic appeal of the city's lighting. The luminaire's timeless design comes in two sizes – mini and large – to ensure that the dimensions of the luminaire and pole are well balanced, and that the installation blends in harmoniously with its surroundings. A variety of suspensions are available, offering maximum freedom in the overall design of the installation. A choice of symmetrical or asymmetrical distributions and state-of-the-art LED technology complete the specification of an extremely adaptable luminaire.

Product data

General Information		the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Lamp family code	GRN39 [LED GreenLine 3900 lm]		
Light source replaceable	Yes		
Number of gear units	1 unit		
Driver included	Yes		
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires – January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore,		
		Light source engine type	LED
		Product family code	BRS443 [Little Copenhagen LED side entry]
		Lighting Technology	LED
		Embedded control	Constant light output and DynaDimmer fixed presets version 6

Copenhagen LED Small

CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0
Luminous Flux	3,280 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	115 lm/W
Color rendering index (CRI)	≥70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution wet road (DK)

Operating and Electrical

Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	25 W
Average CLO power consumption	28 W
End CLO power consumption	32 W
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	32 W
Power Factor (Fraction)	0.9
Connection	-
Cable	Cable 10 m without plug
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit with DynaDimmer and constant light output (integrated)
Control interface	-
Constant light output	Yes

Mechanical and Housing

Reflector material	-
--------------------	---

Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Side-entry for diameter 48 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall height	312 mm
Overall diameter	380 mm
Effective projected area	0.08 m²

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.382, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BRS443 GRN39- 3S/740 II DK GR CLO-DDF6
Full product name	BRS443 GRN39- 3S/740 II DK GR CLO-DDF6
Full product code	871829156070800
Order code	56070800
Material Nr. (12NC)	919008632018
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291560708
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291560708

Copenhagen LED Small

Dimensional drawing

