



Copenhagen LED Small

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Upward light output ratio	0
Luminous Flux	2,480 lumen
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	113 lm/W
Color rendering index (CRI)	≥70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution comfort

Operating and Electrical

Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	13 W
Average CLO power consumption	14 W
End CLO power consumption	16 W
Inrush current	27 A
Inrush time	0.265 ms
Power Consumption	16 W
Power Factor (Fraction)	0.9
Connection	-
Cable	Cable 10 m without plug
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit with DynaDimmer and constant light output (integrated)
Control interface	-
Constant light output	Yes

Mechanical and Housing

Reflector material	-
Optic material	Polycarbonate

Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Side-entry for diameter 48 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall height	312 mm
Overall diameter	380 mm
Effective projected area	0.08 m²

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.382, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Full product code	871829198758100
Order product name	BRS443 GRN20-3S/740 II DC GR CLO-DDF6
Order code	919008632298
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	919008632298
Full product name	BRS443 GRN20-3S/740 II DC GR CLO-DDF6
EAN/UPC - Case	8718291987581
EAN/UPC - Product/Case	8718291987581

Copenhagen LED Small

Dimensional drawing

