



Copenhagen LED Big

BRS441 GRN68-3S/740 II O-DK CLO-DDF6 C10

Big Copenhagen LED side entry, LED GreenLine 6800 lm, 740 neutral white, Safety class II, Distribution wet road (DK), Constant light output and DynaDimmer fixed presets version 6, Cable 10 m without plug

Copenhagen LED was co-designed together with Copenhagen's Office of City Architecture in order to enhance the aesthetic appeal of the city's lighting. The luminaire's timeless design comes in two sizes – mini and large – to ensure that the dimensions of the luminaire and pole are well balanced, and that the installation blends in harmoniously with its surroundings. A variety of suspensions are available, offering maximum freedom in the overall design of the installation. A choice of symmetrical or asymmetrical distributions and state-of-the-art LED technology complete the specification of an extremely adaptable luminaire.

Product data

General Information			
Lamp family code	GRN68 [LED GreenLine 6800 lm]		automatically dim down to protect components
Light source replaceable	Yes	Light source engine type	LED
Number of gear units	1 unit	Product family code	BRS441 [Big Copenhagen LED side entry]
Driver included	Yes	Lighting Technology	LED
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might	Embedded control	Constant light output and DynaDimmer fixed presets version 6
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	-
		EU RoHS compliant	Yes

Copenhagen LED Big

Light Technical	
Upward light output ratio	0
Luminous Flux	5,760 lumen
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color rendering index (CRI)	≥70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution wet road (DK)
Operating and Electrical	
Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	46 W
Average CLO power consumption	52 W
End CLO power consumption	57 W
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	57 W
Power Factor (Fraction)	0.9
Connection	-
Cable	Cable 10 m without plug
Number of products on MCB of 16 A type B	8
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit with DynaDimmer and constant light output (integrated)
Control interface	-
Constant light output	Yes
Mechanical and Housing	
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum

Housing Color	Opal
Mounting device	Side-entry for diameter 48 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall height	367 mm
Overall diameter	462 mm
Effective projected area	0.13 m²
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.382, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100
Application Conditions	
Performance ambient temperature Tq	25 °C
Product Data	
Full product code	871829198799400
Order product name	BRS441 GRN68-3S/740 II O-DK CLO-DDF6 C10
Order code	919008632307
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	919008632307
Full product name	BRS441 GRN68-3S/740 II O-DK CLO-DDF6 C10
EAN/UPC - Case	8718291987994
EAN/UPC - Product/Case	8718291987994

Copenhagen LED Big

