



# Copenhagen LED Small

## BRS443 GRN39-3S/740 II O-DP-R CLO-DDF6

Little Copenhagen LED side entry, LED GreenLine 3900 lm, 740 neutral white, Safety class II, Distribution pedestrian crossing right, Constant light output and DynaDimmer fixed presets version 6, Cable 10 m without plug

Copenhagen LED was co-designed together with Copenhagen's Office of City Architecture in order to enhance the aesthetic appeal of the city's lighting. The luminaire's timeless design comes in two sizes – mini and large – to ensure that the dimensions of the luminaire and pole are well balanced, and that the installation blends in harmoniously with its surroundings. A variety of suspensions are available, offering maximum freedom in the overall design of the installation. A choice of symmetrical or asymmetrical distributions and state-of-the-art LED technology complete the specification of an extremely adaptable luminaire.

### Product data

General Information		the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Lamp family code	GRN39 [LED GreenLine 3900 lm]		
Light source replaceable	Yes		
Number of gear units	1 unit		
Driver included	Yes		
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore,		
		Light source engine type	LED
		Product family code	BRS443 [Little Copenhagen LED side entry]
		Lighting Technology	LED
		Embedded control	Constant light output and DynaDimmer fixed presets version 6

# Copenhagen LED Small

CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
EU RoHS compliant	Yes

## Light Technical

Upward light output ratio	0
Luminous Flux	3,280 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	95 lm/W
Color rendering index (CRI)	≥70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution pedestrian crossing right

## Operating and Electrical

Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	30 W
Average CLO power consumption	33 W
End CLO power consumption	37 W
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	33 W
Power Factor (Fraction)	0.9
Connection	-
Cable	Cable 10 m without plug
Number of products on MCB of 16 A type B	20

## Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit with DynaDimmer and constant light output (integrated)
Control interface	-
Constant light output	Yes

## Mechanical and Housing

Reflector material	-
--------------------	---

Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Opal
Mounting device	Side-entry for diameter 48 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall height	312 mm
Overall diameter	380 mm
Effective projected area	0.08 m²

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.382, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

## Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

## Product Data

Order product name	BRS443 GRN39-3S/740 II O-DP-R CLO-DDF6
Full product name	BRS443 GRN39-3S/740 II O-DP-R CLO-DDF6
Full product code	871829198950900
Order code	98950900
Material Nr. (12NC)	919008632347
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291989509
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291989509

## Copenhagen LED Small

### Dimensional drawing

