



# Copenhagen LED Big

## BRS441 GRN48-3S/830II O-DK CLO-DDF6 C10K

Big Copenhagen LED side entry, LED GreenLine 4800 lm, 830 warm white, Safety class II, Distribution wet road (DK), Constant light output and DynaDimmer fixed presets version 6, Cable 10 m without plug

Copenhagen LED was co-designed together with Copenhagen's Office of City Architecture in order to enhance the aesthetic appeal of the city's lighting. The luminaire's timeless design comes in two sizes – mini and large – to ensure that the dimensions of the luminaire and pole are well balanced, and that the installation blends in harmoniously with its surroundings. A variety of suspensions are available, offering maximum freedom in the overall design of the installation. A choice of symmetrical or asymmetrical distributions and state-of-the-art LED technology complete the specification of an extremely adaptable luminaire.

### Product data

General Information			
Lamp family code	GRN48 [LED GreenLine 4800 lm]		might automatically dim down to protect components
Light source replaceable	Yes	Light source engine type	LED
Number of gear units	1 unit	Product family code	BRS441 [Big Copenhagen LED side entry]
Driver included	Yes	Lighting Technology	LED
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire	Embedded control	Constant light output and DynaDimmer fixed presets version 6
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	-
		EU RoHS compliant	Yes

# Copenhagen LED Big

<b>Light Technical</b>	
Upward light output ratio	0
Luminous Flux	4,000 lumen
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	97 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Light source color	830 warm white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution wet road (DK)
<b>Operating and Electrical</b>	
Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	41 W
Average CLO power consumption	46 W
End CLO power consumption	51 W
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	46 W
Power Factor (Fraction)	0.9
Connection	-
Cable	Cable 10 m without plug
Number of products on MCB of 16 A type 8 B	
<b>Temperature</b>	
Ambient temperature range	-40 to +50 °C
<b>Controls and Dimming</b>	
Dimmable	No
Driver/power unit/transformer	Power supply unit with DynaDimmer and constant light output (integrated)
Control interface	-
Constant light output	Yes
<b>Mechanical and Housing</b>	
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum

Housing Color	Opal
Mounting device	Side-entry for diameter 48 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall height	367 mm
Overall diameter	462 mm
Effective projected area	0.13 m²
<b>Approval and Application</b>	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.434, 0.403) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
<b>Over Time Performance (IEC Compliant)</b>	
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100
<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
<b>Product Data</b>	
Full product code	871869685911700
Order product name	BRS441 GRN48-3S/830II O-DK CLO-DDF6 C10K
Order code	919008632535
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	919008632535
Full product name	BRS441 GRN48-3S/830II O-DK CLO-DDF6 C10K
EAN/UPC - Case	8718696859117
EAN/UPC - Product/Case	8718696859117

## Copenhagen LED Big

