



MileWide²

BRP435LED22-4S/830I SI DM50 CTGCO 48ST25

MileWide 2 - side entry - LED module 2200 lm - 830 warm white - Safety class I - Distribution medium 50 - Silver - Marine salt protected coating - Cord 0.5 m with cable connector 3-pole - Side-entry for diameter 48 mm

Many municipal authorities are embracing the benefits of contemporary outdoor lighting. These include a more attractive urban environment and increased comfort, safety and security for the public. Not to mention the positive impact on environmental protection and city branding. Together with Holscher Design, Philips has developed MileWide², the successor to the highly popular MileWide family. Featuring a range of dedicated masts and brackets, the pure, clean design of MileWide² integrates perfectly with today's and tomorrow's cityscape. With its high-quality finish and high level of lighting performance, MileWide² is suitable for a wide range of applications, ranging from traffic roads to city centers. Multi-layer optics provide a uniform light distribution and reduced glare, enabling direct replacement of HID solutions without compromising on spacing, mounting height or light quality.

Product data

General Information	
Lamp family code	LED22 [LED module 2200 lm]
Light source colour	830 warm white
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Optical cover/lens type	FG [Flat glass]
Luminaire light beam spread	-
Control interface	GPRS network
Connection	Connection unit 3-pole

Cable	Cord 0.5 m with cable connector 3-pole
Protection class IEC	Safety class I
Coating	Marine salt protected coating
Flammability mark	NO [-]
CE mark	CE mark
ENEC mark	ENEC mark
Outdoor optic type	Distribution medium 50
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Constant light output	No

Number of products on MCB	20
RoHS mark	RoHS mark
LED engine type	LED
Product Family Code	BRP435 [MileWide 2 side entry]

Light Technical

Upward light output ratio	0.03
Standard tilt angle post-top	-
Standard tilt angle side entry	-

Operating and Electrical

Input voltage	220/240 V
Input frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	320 ms
Power factor (min.)	0.99

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Glass
Fixation material	Aluminum
Mounting device	48S [Side-entry for diameter 48 mm]
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	610 mm
Overall width	276 mm
Overall height	135 mm

Effective projected area	0.049 m ²
Colour	Silver

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial Performance (IEC Compliant)


Initial luminous flux	1892 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	102 lm/W
Init. Corr. colour temperature	3000 K
Init. colour rendering index	≥80
Initial chromaticity	(0.430, 0.400) SDCM <5
Initial input power	18.6 W
Power consumption tolerance	+/-11%

Application Conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product Data

Full product code	871869958038400
Order product name	BRP435LED22-4S/830I SI DM50 CTGCO 48ST25
EAN/UPC – product	8718699580384
Order code	58038400
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	919008633651
Net weight (piece)	5.740 kg



Dimensional drawing



MileWide2 BPP/BRP435

