



EcoBATTEN 2

TMS950 2XTL5-25W WR

2, TL5, 25 W, White reflector without louver

EcoBATTEN 2 is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25 W or 50 W TL5 Eco fluorescent tube lamps. Available in 4 body versions and with dimmer-controlled drivers, it allows complete integration with building control systems.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	-
Light Technical	
Number of light sources	2
Light source color	-
Optic type	White reflector without louver
Optical cover type	-
Operating and Electrical	
Power Consumption	25 W

Mechanical and Housing	
Housing Color	White
Product Data	
Order product name	TMS950 2XTL5-25W WR
Full product name	TMS950 2XTL5-25W WR
Order code	919106020611
Material Nr. (12NC)	919106020611
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1