



# EcoBATTEN 2

## TMS952 2XTL5-50W/840 EB R-H WH

2, TL5, 50 W, 840 neutral white, Electronic, Reflector high reflectance, White

EcoBATTEN 2 is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25 W or 50 W TL5 Eco fluorescent tube lamps. Available in 4 body versions and with dimmer-controlled drivers, it allows complete integration with building control systems.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	Reflector high reflectance
Optical cover type	-
Operating and Electrical	
Power Consumption	50 W

Mechanical and Housing	
Housing Color	White
Product Data	
Order product name	TMS952 2XTL5-50W/840 EB R-H WH
Full product name	TMS952 2XTL5-50W/840 EB R-H WH
Order code	919106020691
Material Nr. (12NC)	919106020691
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1