



EcoBATTEN 2

TMS953 2XTL5-25W/840 EB R-H WH AC

2, TL5, 25 W, 840 neutral white, Electronic, Reflector high reflectance, Acrylic bowl/cover, White

EcoBATTEN 2 is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25 W or 50 W TL5 Eco fluorescent tube lamps. Available in 4 body versions and with dimmer-controlled drivers, it allows complete integration with building control systems.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	Reflector high reflectance
Optical cover type	Acrylic bowl/cover
Operating and Electrical	
Power Consumption	25 W

Mechanical and Housing	
Housing Color	White
Product Data	
Order product name	TMS953 2XTL5-25W/840 EB R-H WH AC
Full product name	TMS953 2XTL5-25W/840 EB R-H WH AC
Order code	919106020711
Material Nr. (12NC)	919106020711
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1