



Europa

FBS675 2xPL-C/4P18W/840 EB DG WH

2, MASTER PL-C 4 Pin, 18 W, 840 neutral white, Electronic,
Decorative glass, White

The Europa range offers high performance and an attractive design. It offers an effective solution for various types of commercial establishments since it optimizes the use of electrical energy whilst also ensuring visual comfort. The downlighters of the Europa range create a pleasant and inviting atmosphere, making the lighting an excellent way to promote sales.

Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optical cover type	Decorative glass
Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	18 W

Mechanical and Housing	
Housing Color	White
Product Data	
Order product name	FBS675 2xPL-C/4P18W/840 EB DG WH
Full product name	FBS675 2xPL-C/4P18W/840 EB DG WH
Full product code	919106031099
Order code	919106031099
Material Nr. (12NC)	919106031099
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400002206
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400002206

Dimensional drawing

Torino / Milano

