




TCW060 A

TCW060 2XTL-D32W/840 EB ABS-PC-L

2, MASTER TL-D, 32 W, 840 neutral white, Electronic, Polycarbonate bowl/cover

The new TCW060 hermetic luminaire is ideal for use in harsh environments where protection against vapor, water, and dust is required. It has been specially designed and developed for use with TL-D / TL5 tubular fluorescent lamps and electronic ballasts. Its compact and economical design provides perfect integration with the environment. The IP65 protection means the TCW060 is waterproof, enabling it to be used in damp places such as in industry, warehouses, garages, etc. It is easy to install and maintain because it has adjustable ceiling clips to make installation even more flexible and practical.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optical cover type	Polycarbonate bowl/cover
Operating and Electrical	
Power Consumption	32 W

Product Data	
Order product name	TCW060 2XTL-D32W/840 EB ABS-PC-L
Full product name	TCW060 2XTL-D32W/840 EB ABS-PC-L
Full product code	919106031571
Order code	919106031571
Material Nr. (12NC)	919106031571
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400001162
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400001162

TCW060 A

Dimensional drawing

