



Europa

MBS675 1xMHN-TD70W/842 DG WH

1, MHN-TD, 70 W, 842 neutral white, Decorative glass, White

The Europa range offers high performance and an attractive design. It offers an effective solution for various types of commercial establishments since it optimizes the use of electrical energy whilst also ensuring visual comfort. The downlighters of the Europa range create a pleasant and inviting atmosphere, making the lighting an excellent way to promote sales.

Product data

General Information	
Lamp family code	MHN-TD
Light Technical	
Number of light sources	1
Light source color	842 neutral white
Optical cover type	Decorative glass
Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	70 W

Mechanical and Housing	
Housing Color	White
Product Data	
Order product name	MBS675 1xMHN-TD70W/842 DG WH
Full product name	MBS675 1xMHN-TD70W/842 DG WH
Full product code	919306012561
Order code	919306012561
Material Nr. (12NC)	919306012561
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

Firenze

