



Europa

MBS675 1XCDM-TD150W/830 EB DG WH

1, MASTERColour CDM-TD, 150 W, 830 warm white, Decorative glass, White

The Europa range offers high performance and an attractive design. It offers an effective solution for various types of commercial establishments since it optimizes the use of electrical energy whilst also ensuring visual comfort. The downlighters of the Europa range create a pleasant and inviting atmosphere, making the lighting an excellent way to promote sales.

Product data

General Information	
Lamp family code	CDM-TD [MASTERColour CDM-TD]
Light Technical	
Number of light sources	1
Light source color	830 warm white
Optical cover type	Decorative glass
Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	150 W
Mechanical and Housing	
Housing Color	White

Product Data	
Order product name	MBS675 1XCDM-TD150W/830 EB DG WH
Full product name	MBS675 1XCDM-TD150W/830 EB DG WH
Full product code	919306012591
Order code	919306012591
Material Nr. (12NC)	919306012591
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400002220
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400002220

Dimensional drawing

Firenze

