



Europa

FBS672 2XPL-C/2P18W/840 220V-60Hz GF WH

2, MASTER PL-C 2 Pin, 18 W, 840 neutral white, 220 V, 60 Hz, 60 Hz, Glass frosted, White

The Europa range offers high performance and an attractive design. It offers an effective solution for various types of commercial establishments since it optimizes the use of electrical energy whilst also ensuring visual comfort. The downlighters of the Europa range create a pleasant and inviting atmosphere, making the lighting an excellent way to promote sales.

Product data

General Information		Mechanical and Housing	
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]	Housing Color	White
Light Technical		Product Data	
Number of light sources	2	Order product name	FBS672 2XPL-C/2P18W/840 220V-60Hz GF WH
Light source color	840 neutral white	Full product name	FBS672 2XPL-C/2P18W/840 220V-60Hz GF WH
Optical cover type	Glass frosted	Full product code	919306012601
Operating and Electrical		Order code	919306012601
Input Voltage	220 V	Material Nr. (12NC)	919306012601
Line Frequency	60 Hz	Numerator - Quantity Per Pack	1
Input Frequency	60 Hz	Numerator - Packs per outer box	1
Power Consumption	18 W		

Dimensional drawing

Torino / Milano

