



Europa

FBS675 2xPL-C/2P18W/840 220V-60HZ DG WH

2, MASTER PL-C 2 Pin, 18 W, 220 V, 60 Hz, 60 Hz, White

The Europa range offers high performance and an attractive design. It offers an effective solution for various types of commercial establishments since it optimizes the use of electrical energy whilst also ensuring visual comfort. The downlighters of the Europa range create a pleasant and inviting atmosphere, making the lighting an excellent way to promote sales.

Product data

General Information	
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]
Light Technical	
Number of light sources	2
Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	18 W
Mechanical and Housing	
Housing Color	White

Product Data	
Order product name	FBS675 2xPL-C/2P18W/840 220V-60HZ DG WH
Full product name	FBS675 2xPL-C/2P18W/840 220V-60HZ DG WH
Full product code	919306012628
Order code	919306012628
Material Nr. (12NC)	919306012628
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

Torino / Milano

