



# D'ECO Light Collection

## FBS320/321/323/331

### FBS321 1XPL-C/2P18W/840 220V-60HZ GF WH

1, MASTER PL-C 2 Pin, 18 W, 840 neutral white, 220 V, 60 Hz, 60 Hz, Glass frosted, White

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design, it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

#### Product data

<b>General Information</b>		<b>Power Consumption</b>	
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]	18 W	
<b>Light Technical</b>		<b>Mechanical and Housing</b>	
Number of light sources	1	Housing Color	
Light source color	840 neutral white	White	
Optical cover type	Glass frosted	<b>Product Data</b>	
<b>Operating and Electrical</b>		Order product name	
Input Voltage	220 V	FBS321 1XPL-C/2P18W/840 220V-60HZ GF WH	
Line Frequency	60 Hz	Full product name	
Input Frequency	60 Hz	FBS321 1XPL-C/2P18W/840 220V-60HZ GF WH	
		Full product code	
		919406003901	
		Order code	
		919406003901	
		Material Nr. (12NC)	
		919406003901	
		Numerator - Quantity Per Pack	
		1	
		Numerator - Packs per outer box	
		1	

## D'ECO Light Collection FBS320/321/323/331

---

### Dimensional drawing

