



D'ECO Light Collection

FBS320/321/323/331

FBS321 2XPL-C/2P18W/840 220V-60HZ GF WH

2, MASTER PL-C 2 Pin, 18 W, 840 neutral white, 220 V, 60 Hz, 60 Hz, Glass frosted, White

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design, it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

Product data

General Information		Power Consumption	
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]	18 W	
Light Technical		Mechanical and Housing	
Number of light sources	2	Housing Color	White
Light source color	840 neutral white	Product Data	
Optical cover type	Glass frosted	Order product name	FBS321 2XPL-C/2P18W/840 220V-60HZ GF WH
Operating and Electrical		Full product name	FBS321 2XPL-C/2P18W/840 220V-60HZ GF WH
Input Voltage	220 V	Full product code	919406003921
Line Frequency	60 Hz	Order code	919406003921
Input Frequency	60 Hz	Material Nr. (12NC)	919406003921
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1

D'ECO Light Collection FBS320/321/323/331

Dimensional drawing

