



# SLS1500

## MVP158 E40 MAX1500W R-WB IP55

Reflector wide beam

SLS projectors are lightweight and compact. Ideal for outdoor lighting, they are designed for use with 1500 W metal-halide lamps or 1000 W sodium vapor lamps. They are available in two beam apertures: open and closed. A high-gloss aluminum reflector with enclosed glass front provides protection against dust. They are easy to install and deliver excellent lighting performance.

### Product data

<b>General Information</b>		<b>Full product name</b>	MVP158 E40 MAX1500W R-WB IP55
Cap-Base	E40 [E40]	Full product code	919506010153
<b>Light Technical</b>		Order code	919506010153
Optic type outdoor	Reflector wide beam	Material Nr. (12NC)	919506010153
<b>Approval and Application</b>		Numerator - Quantity Per Pack	1
Ingress protection code	IP55 [Dust accumulation-protected, jet-proof]	EAN/UPC - Product/Case	7894400003395
<b>Product Data</b>		Numerator - Packs per outer box	1
Order product name	MVP158 E40 MAX1500W R-WB IP55	EAN/UPC - Case	7894400003395

## SLS1500

### Dimensional drawing

Dimensões em mm:

