



GreenPerform DN391/392/393/394/ 395 downlight

DN 391B LED6S-6500 PSR WH

GreenPerform is a high performance Led downlight family suitable for use in a series of Lighting applications in Office, Retail and General Area Lighting. Available in a wide variety of lumen packs, color temp and options of all type of dimming(Phase Cut/Analogue/DALI), GreenPerform becomes the perfect solution for downlight applications for professional users.

Warnings and Safety

- Meant for use in Indoor environment only

Product data

Light Technical		Temperature	
Correlated Color Temperature (Nom)	6500 K	Ambient temperature range	0 to +45 °C
Color rendering index (CRI)	>80		
Light source color	865 cool daylight	Controls and Dimming	
Luminaire light beam spread	110°	Dimmable	Yes
		Control interface	Analog
Operating and Electrical		Mechanical and Housing	
Input Voltage	220-240 V	Housing Material	Aluminum die cast
Line Frequency	50 Hz	Housing Color	White
Power Consumption	6.5 W	Overall height	60 mm
Power Factor (Fraction)	0.9	Overall diameter	100 mm
		Material	Aluminum

GreenPerform DN391/392/393/394/395 downlight

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	DN 391B LED6S-6500 PSR WH
Full product name	DN 391B LED6S-6500 PSR WH
Order code	919515810430
Material Nr. (12NC)	919515810430
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Dimensional drawing

Product: GNI
Type: DN391B / DN392B / DN393B / DN394B / DN395B
Application: Indoor

