



# GreenPerform DN391/392/393/394/ 395 downlight

## DN 394B LED16S-4000 PSR WH

GreenPerform is a high performance Led downlight family suitable for use in a series of Lighting applications in Office, Retail and General Area Lighting. Available in a wide variety of lumen packs, color temp and options of all type of dimming(Phase Cut/Analogue/DALI), GreenPerform becomes the perfect solution for downlight applications for professional users.

### Warnings and Safety

- Meant for use in Indoor environment only

### Product data

<b>Light Technical</b>		<b>Temperature</b>	
Correlated Color Temperature (Nom)	4000 K	Ambient temperature range	0 to +45 °C
Color rendering index (CRI)	>80	<b>Controls and Dimming</b>	
Light source color	840 neutral white	Dimmable	Yes
Luminaire light beam spread	110°	Control interface	Analog
<b>Operating and Electrical</b>		<b>Mechanical and Housing</b>	
Input Voltage	220-240 V	Housing Material	Aluminum die cast
Line Frequency	50 Hz	Housing Color	White
Power Consumption	15.5 W	Overall height	80 mm
Power Factor (Fraction)	0.9	Overall diameter	185 mm
		Material	Aluminum

# GreenPerform DN391/392/393/394/395 downlight

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Power consumption tolerance	+/-10%

Product Data	
Order product name	DN 394B LED16S-4000 PSR WH
Full product name	DN 394B LED16S-4000 PSR WH
Order code	919515810438
Material Nr. (12NC)	919515810438
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

## Dimensional drawing

Product: GNI  
Type: DN391B / DN392B / DN393B / DN394B / DN395B  
Application: Indoor

