



GreenPerform DN391/392/393/394/ 395 downlight

DN 391B LED6S-3000 PSR WH

GreenPerform is a high performance Led downlight family suitable for use in a series of Lighting applications in Office, Retail and General Area Lighting. Available in a wide variety of lumen packs, color temp and options of all type of dimming(Phase Cut/Analogue/DALI), GreenPerform becomes the perfect solution for downlight applications for professional users.

Warnings and Safety

- Meant for use in Indoor environment only

Product data

Light Technical		Temperature	
Correlated Color Temperature (Nom)	3000 K	Ambient temperature range	0 to +45 °C
Color rendering index (CRI)	>80	Controls and Dimming	
Light source color	830 warm white	Dimmable	Yes
Luminaire light beam spread	110°	Control interface	Analog
Operating and Electrical		Mechanical and Housing	
Input Voltage	220-240 V	Housing Material	Aluminum die cast
Line Frequency	50 Hz	Housing Color	White
Power Consumption	6.5 W	Overall height	60 mm
Power Factor (Fraction)	0.9	Overall diameter	100 mm
		Material	Aluminum

