



EcoAccent ST271T

ST271T LED20/840 PSU-E MB 1C BK

EcoAccent is the LED solution for shop targeting energy savings. With a system efficacy of 95 lm/W in average, delivering more than 40% energy efficient compared to CDM solution. EcoAccent helps save energy and at the same time provides excellent lighting for retail environment thus enhancing the retail experience. The option of different light distribution for Accent light and variety of lumen packs and colour temperatures makes it an ideal solution for retail lighting.

Product data

| General Information | |
|-----------------------------|----------------------|
| Light source color | 840 neutral white |
| Luminaire light beam spread | 24° |
| Control interface | - |
| Protection class IEC | Safety class II (II) |
| Material | Aluminum |
| Operating and Electrical | |
| Input Voltage | 240 V |
| Input Frequency | 50 Hz |
| Power Factor (Min) | 0.9 |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Housing Material | Aluminum die-cast |
| Overall width | 163 mm |
| Overall height | 225 mm |
| Overall diameter | 85 mm |

| Color | Black |
|--|--------------------------|
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Surge Protection (Common/Differential) | 2.5 kV |

| Initial Performance (IEC Compliant) | |
|-------------------------------------|--------|
| Init. Corr. Color Temperature | 4000 K |
| Init. Color Rendering Index | >80 |
| Initial input power | 22 W |
| Power consumption tolerance | +/-10% |

| Over Time Performance (IEC Compliant) | |
|---------------------------------------|---------|
| Median useful life L70B50 | 30000 h |


| Application Conditions | |
|---------------------------|-------------|
| Ambient temperature range | 0 to +45 °C |

| Product Data | |
|--------------------|---------------------------------|
| Order product name | ST271T LED20/840 PSU-E MB 1C BK |

EcoAccent ST271T

| | |
|---------------------------------|--------------|
| Order code | 919515810929 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 919515810929 |

| | |
|--------------------|----------|
| Net Weight (Piece) | 0.750 kg |
|--------------------|----------|




Warnings and Safety

- To be used in Indoor Environment only

Dimensional drawing

Product: XRA TRACK MOUNTED
Type: ST271 T
Application: Indoor



IN9002RDL - Downlights and spots

