



# EcoAccent RC271B

## RS271B LED40/850 PSU-E MB WH

EcoAccent is the LED solution for shop lighting targeting energy savings. With a system efficacy of 95 lm/W in average, delivers more than 40% energy efficient compared to CDM solution. EcoAccent helps save energy and at the same time provides excellent lighting for retail environment thus enhancing the retail experience. The option of different light distribution for Accent light and variety of lumen packs and colour temperatures makes it an ideal solution for retail lighting.

### Warnings and Safety

- To be used in Indoor Environment only

### Product data

General Information		Operating and Electrical	
Driver included	Yes	Input Voltage	240 V
Light source engine type	LED	Line Frequency	50 Hz
Warranty period	3 years	Power Consumption	42 W
Flammability mark	For mounting on normally flammable surfaces	Power Factor (Fraction)	0.9
Light Technical		Temperature	
Luminous Flux	4,000 lm	Ambient temperature range	0 to +45 °C
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	100 lm/W	Controls and Dimming	
Color rendering index (CRI)	>80	Dimmable	No
Beam angle of light source	24 degree(s)	Control interface	-
Light source color	840 neutral white		
Optic type	Beam angle 12 to 36°	Mechanical and Housing	
Optical cover type	Aluminum and polycarbonate	Housing Material	Aluminum Alloy
Luminaire light beam spread	24°	Optic material	Aluminum and polycarbonate
		Optical cover material	Polycarbonate
		Housing Color	White

# EcoAccent RC271B

Mounting device	Mounting bracket adjustable
Overall height	142 mm
Overall diameter	195 mm
Material	Aluminum

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Power consumption tolerance	+/-10%
-----------------------------	--------

## Over Time Performance (IEC Compliant)

Median useful life L70B50	40,000 hour(s)
---------------------------	----------------

## Product Data

Order product name	RS271B LED40/850 PSU-E MB WH
Full product name	RS271B LED40/850 PSU-E MB WH
Order code	919515810959
Material Nr. (12NC)	919515810959
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

Product: XTRA RECESSED  
Type: RC271B  
Application: Indoor

