



Pureline SP680P

SP680X2 LED39S 6500 PSU WH L120 S1

The PureLine family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting . The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

Warnings and Safety

- Meant for use in Indoor environment only

Product data

| | | | |
|------------------------------------|---|--|--|
| General Information | | Power Consumption | |
| Driver included | Yes | 38 W | |
| Light source engine type | LED | Power Factor (Fraction) | |
| Warranty period | 3 years | 0.9 | |
| Flammability mark | For mounting on normally flammable surfaces | Temperature | |
| Light Technical | | Ambient temperature range | |
| Luminous Flux | 3,900 lm | 0 to +45 °C | |
| Correlated Color Temperature (Nom) | 6500 K | Controls and Dimming | |
| Luminous Efficacy (rated) (Nom) | 100 lm/W | Dimmable | |
| Color rendering index (CRI) | >80 | No | |
| Beam angle of light source | 120 degree(s) | Control interface | |
| Light source color | 865 cool daylight | - | |
| Optic type | - | Mechanical and Housing | |
| Optical cover type | Polycarbonate | Housing Material | |
| Luminaire light beam spread | 120° | Aluminum extruded | |
| Operating and Electrical | | Optic material | |
| Input Voltage | 220-240 V | Polycarbonate | |
| Line Frequency | 50 Hz | Optical cover material | |
| | | Polycarbonate | |
| | | Housing Color | |
| | | White | |
| | | Mounting device | |
| | | Suspension set simple, standard | |
| | | Overall length | |
| | | 1,126 mm | |
| | | Overall width | |
| | | 150 mm | |
| | | Overall height | |
| | | 43 mm | |
| | | Dimensions (Height x Width x Depth) | |
| | | 43 x 150 x 1126 mm | |

Pureline SP680P

| | |
|--|-------------------------|
| Material | Aluminum |
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Surge Protection (Common/Differential) | 2.5 kV |
| Protection class IEC | Safety class I |
| Initial Performance (IEC Compliant) | |
| Power consumption tolerance | +/-10% |
| Over Time Performance (IEC Compliant) | |
| Median useful life L70B50 | 50,000 hour(s) |

| | |
|---------------------------------|------------------------------------|
| Product Data | |
| Order product name | SP680X2 LED39S 6500 PSU WH L120 S1 |
| Full product name | SP680X2 LED39S 6500 PSU WH L120 S1 |
| Order code | 919515811498 |
| Material Nr. (12NC) | 919515811498 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Dimensional drawing

Product: Pureline Suspended
Type: SP680
Application: Indoor

