



Pureline SP680P

SP680X2 LED78S 6500 PSU WH L240 S1

The PureLine family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting . The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

Warnings and Safety

- Meant for use in Indoor environment only

Product data

General Information		Power Consumption	
Driver included	Yes	Power Factor (Fraction)	0.9
Light source engine type	LED	Temperature	
Warranty period	3 years	Ambient temperature range	0 to +45 °C
Flammability mark	For mounting on normally flammable surfaces	Controls and Dimming	
Light Technical		Dimmable	No
Luminous Flux	7,800 lm	Control interface	-
Correlated Color Temperature (Nom)	6500 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	100 lm/W	Housing Material	Aluminum extruded
Color rendering index (CRI)	>80	Optic material	Polycarbonate
Beam angle of light source	120 degree(s)	Optical cover material	Polycarbonate
Light source color	865 cool daylight	Housing Color	White
Optic type	-	Mounting device	Suspension set simple, standard
Optical cover type	Polycarbonate	Overall length	4,564 mm
Luminaire light beam spread	120°	Overall width	150 mm
Operating and Electrical		Overall height	43 mm
Input Voltage	220-240 V	Dimensions (Height x Width x Depth)	43 x 150 x 4564 mm
Line Frequency	50 Hz		

Pureline SP680P

Material	Aluminum
----------	----------

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Power consumption tolerance	+/-10%
-----------------------------	--------

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Product Data	
Order product name	SP680X2 LED78S 6500 PSU WH L240 S1
Full product name	SP680X2 LED78S 6500 PSU WH L240 S1
Order code	919515811510
Material Nr. (12NC)	919515811510
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

Product: Pureline Suspended
Type: SP680
Application: Indoor

