



Pureline SP680P

SP680X1 LED68S 6500 PSU WH L240 S1

The PureLine family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting. The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.


Product data

General Information	
Light source color	865 cool daylight
Luminaire light beam spread	110°
Control interface	-
Protection class IEC	Safety class I (I)
Material	Aluminum
Operating and Electrical	
Input Voltage	220-240 V
Input Frequency	50 Hz
Power Factor (Min)	0.9
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Material	Aluminum extruded
Overall length	9128 mm
Overall width	150 mm
Overall height	43 mm
Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Initial Performance (IEC Compliant)	
Init. Corr. Color Temperature	6500 K
Init. Color Rendering Index	>80
Initial input power	64 W
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	50000 h
Application Conditions	
Ambient temperature range	0 to +45 °C
Product Data	
Order product name	SP680X1 LED68S 6500 PSU WH L240 S1
Order code	919515811512
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	919515811512

Pureline SP680P

Net Weight (Piece) 5.000 kg




Warnings and Safety

- Meant for use in Indoor environment only

Dimensional drawing

Product: Pureline Suspended
Type: SP680
Application: Indoor



IN9002SUS - Suspended luminaires

