



# Pureline SP680P

## SP680X2 LED78S 4000 PSU WH L240 S1

The PureLine family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting. The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

### Warnings and Safety

- Meant for use in Indoor environment only

### Product data

General Information		Power Consumption	
Driver included	Yes	Power Consumption	76 W
Light source engine type	LED	Power Factor (Fraction)	0.9
Warranty period	3 years	<b>Temperature</b>	
Flammability mark	For mounting on normally flammable surfaces	Ambient temperature range	0 to +45 °C
<b>Light Technical</b>		<b>Controls and Dimming</b>	
Luminous Flux	7,800 lm	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	100 lm/W	<b>Mechanical and Housing</b>	
Color rendering index (CRI)	>80	Housing Material	Aluminum extruded
Beam angle of light source	120 degree(s)	Optic material	Polycarbonate
Light source color	840 neutral white	Optical cover material	Polycarbonate
Optic type	-	Housing Color	White
Optical cover type	Polycarbonate	Mounting device	Suspension set simple, standard
Luminaire light beam spread	120°	Overall length	4,564 mm
<b>Operating and Electrical</b>		Overall width	150 mm
Input Voltage	220-240 V	Overall height	43 mm
Line Frequency	50 Hz	Dimensions (Height x Width x Depth)	43 x 150 x 4564 mm

# Pureline SP680P

<b>Material</b>	Aluminum
-----------------	----------

## Approval and Application

<b>Ingress protection code</b>	IP20 [Finger-protected]
<b>Mech. impact protection code</b>	IK02 [0.2 J standard]
<b>Surge Protection (Common/Differential)</b>	2.5 kV
<b>Protection class IEC</b>	Safety class I

## Initial Performance (IEC Compliant)

<b>Power consumption tolerance</b>	+/-10%
------------------------------------	--------

## Over Time Performance (IEC Compliant)

<b>Median useful life L70B50</b>	50,000 hour(s)
----------------------------------	----------------

## Product Data

<b>Order product name</b>	SP680X2 LED78S 4000 PSU WH L240 S1
<b>Full product name</b>	SP680X2 LED78S 4000 PSU WH L240 S1
<b>Order code</b>	919515811516
<b>Material Nr. (12NC)</b>	919515811516
<b>Numerator - Quantity Per Pack</b>	1
<b>Numerator - Packs per outer box</b>	1

## Dimensional drawing

Product: Pureline Suspended  
Type: SP680  
Application: Indoor

