



Pureline SP680P

SP680X2 LED68S 4000 PSU WH L240 S1

The PureLine family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting . The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

Warnings and Safety

- Meant for use in Indoor environment only

Product data

General Information		Power Consumption	
Driver included	Yes	64 W	
Light source engine type	LED	Power Factor (Fraction)	
Warranty period	3 years	0.9	
Flammability mark	For mounting on normally flammable surfaces	Temperature	
Light Technical		Ambient temperature range	
Luminous Flux	6,800 lm	0 to +45 °C	
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	100 lm/W	Dimmable	
Color rendering index (CRI)	>80	No	
Beam angle of light source	120 degree(s)	Control interface	
Light source color	840 neutral white	-	
Optic type	-	Mechanical and Housing	
Optical cover type	Polycarbonate	Housing Material	
Luminaire light beam spread	120°	Aluminum extruded	
Operating and Electrical		Optic material	
Input Voltage	220-240 V	Polycarbonate	
Line Frequency	50 Hz	Optical cover material	
		Polycarbonate	
		Housing Color	
		White	
		Mounting device	
		Suspension set simple, standard	
		Overall length	
		4,564 mm	
		Overall width	
		150 mm	
		Overall height	
		43 mm	
		Dimensions (Height x Width x Depth)	
		43 x 150 x 4564 mm	

Pureline SP680P

Material	Aluminum
----------	----------

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Power consumption tolerance	+/-10%
-----------------------------	--------

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Product Data	
Order product name	SP680X2 LED68S 4000 PSU WH L240 S1
Full product name	SP680X2 LED68S 4000 PSU WH L240 S1
Order code	919515811519
Material Nr. (12NC)	919515811519
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

Product: Pureline Suspended
Type: SP680
Application: Indoor

