



# Pureline SP680P

## SP680X1 LED39S 6500 PSD WH L120 S1

The PureLine family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting . The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

### Warnings and Safety

- Meant for use in Indoor environment only

### Product data

<b>General Information</b>		<b>Power Consumption</b>	
Driver included	Yes	38 W	
Light source engine type	LED	<b>Power Factor (Fraction)</b>	
Warranty period	3 years	0.9	
Flammability mark	For mounting on normally flammable surfaces	<b>Temperature</b>	
<b>Light Technical</b>		<b>Ambient temperature range</b>	
Luminous Flux	3,900 lm	0 to +45 °C	
Correlated Color Temperature (Nom)	6500 K	<b>Controls and Dimming</b>	
Luminous Efficacy (rated) (Nom)	100 lm/W	<b>Dimmable</b>	
Color rendering index (CRI)	>80	Yes	
Beam angle of light source	120 degree(s)	<b>Control interface</b>	
Light source color	865 cool daylight	DALI	
Optic type	-	<b>Mechanical and Housing</b>	
Optical cover type	Polycarbonate	<b>Housing Material</b>	
Luminaire light beam spread	120°	Aluminum extruded	
<b>Operating and Electrical</b>		<b>Optic material</b>	
Input Voltage	220-240 V	Polycarbonate	
Line Frequency	50 Hz	<b>Optical cover material</b>	
		Polycarbonate	
		<b>Housing Color</b>	
		White	
		<b>Mounting device</b>	
		Suspension set simple, standard	
		<b>Overall length</b>	
		1,126 mm	
		<b>Overall width</b>	
		150 mm	
		<b>Overall height</b>	
		43 mm	
		<b>Dimensions (Height x Width x Depth)</b>	
		43 x 150 x 1126 mm	

Pureline SP680P

Material	Aluminum
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	50,000 hour(s)

Product Data	
Order product name	SP680X1 LED39S 6500 PSD WH L120 S1
Full product name	SP680X1 LED39S 6500 PSD WH L120 S1
Order code	919515811521
Material Nr. (12NC)	919515811521
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

Product: Pureline Suspended  
Type: SP680  
Application: Indoor

