

# Pureline SP680P

## SP680X2 LED34S 6500 PSD WH L120 S1

The PureLine family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting. The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.


### Product data

General Information	
Light source color	865 cool daylight
Luminaire light beam spread	110°
Control interface	DALI
Protection class IEC	Safety class I (I)
Material	Aluminum
Operating and Electrical	
Input Voltage	220-240 V
Input Frequency	50 Hz
Power Factor (Min)	0.9
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Material	Aluminum extruded
Overall length	1126 mm
Overall width	150 mm
Overall height	43 mm
Color	White

Approval and Application	
Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Initial Performance (IEC Compliant)	
Init. Corr. Color Temperature	6500 K
Init. Color Rendering Index	>80
Initial input power	32 W
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	50000 h
Application Conditions	
Ambient temperature range	0 to +45 °C
Product Data	
Order product name	SP680X2 LED34S 6500 PSD WH L120 S1
Order code	919515811525
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	919515811525

# Pureline SP680P

Net Weight (Piece) 2.600 kg




## Warnings and Safety

- Meant for use in Indoor environment only

## Dimensional drawing

Product: Pureline Suspended  
Type: SP680  
Application: Indoor



### IN9002SUS - Suspended luminaires

