



Pureline SP680P

SP680P LED34S 4000 PSD WH L120 S1

The PureLine family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting . The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

Warnings and Safety

- Meant for use in Indoor environment only

Product data

| General Information | |
|------------------------------------|---|
| Driver included | Yes |
| Light source engine type | LED |
| Warranty period | 3 years |
| Flammability mark | For mounting on normally flammable surfaces |
| Light Technical | |
| Luminous Flux | 3,400 lm |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 100 lm/W |
| Color rendering index (CRI) | >80 |
| Beam angle of light source | 120 degree(s) |
| Light source color | 840 neutral white |
| Optic type | - |
| Optical cover type | Polycarbonate |
| Luminaire light beam spread | 120° |
| Operating and Electrical | |
| Input Voltage | 220-240 V |
| Line Frequency | 50 Hz |

| Power Consumption | 32 W |
|-------------------------------------|---------------------------------|
| Power Factor (Fraction) | 0.9 |
| Temperature | |
| Ambient temperature range | 0 to +45 °C |
| Controls and Dimming | |
| Dimmable | Yes |
| Control interface | DALI |
| Mechanical and Housing | |
| Housing Material | Aluminum extruded |
| Optic material | Polycarbonate |
| Optical cover material | Polycarbonate |
| Housing Color | White |
| Mounting device | Suspension set simple, standard |
| Overall length | 1,156 mm |
| Overall width | 150 mm |
| Overall height | 43 mm |
| Dimensions (Height x Width x Depth) | 43 x 150 x 1156 mm |

Pureline SP680P

| | |
|--|-------------------------|
| Material | Aluminum |
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Surge Protection (Common/Differential) | 2.5 kV |
| Protection class IEC | Safety class I |
| Initial Performance (IEC Compliant) | |
| Power consumption tolerance | +/-10% |
| Over Time Performance (IEC Compliant) | |
| Median useful life L70B50 | 50,000 hour(s) |

| | |
|---------------------------------|-----------------------------------|
| Product Data | |
| Order product name | SP680P LED34S 4000 PSD WH L120 S1 |
| Full product name | SP680P LED34S 4000 PSD WH L120 S1 |
| Order code | 919515811529 |
| Material Nr. (12NC) | 919515811529 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Dimensional drawing

Product: Pureline Suspended
Type: SP680
Application: Indoor

