

# Pureline SP680P

## SP680X2 LED78S 6500 PSD WH L240 S1

The PureLine family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting. The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.


### Product data

| General Information         |                    |
|-----------------------------|--------------------|
| Light source color          | 865 cool daylight  |
| Luminaire light beam spread | 110°               |
| Control interface           | DALI               |
| Protection class IEC        | Safety class I (I) |
| Material                    | Aluminum           |
| Operating and Electrical    |                    |
| Input Voltage               | 220-240 V          |
| Input Frequency             | 50 Hz              |
| Power Factor (Min)          | 0.9                |
| Controls and Dimming        |                    |
| Dimmable                    | Yes                |
| Mechanical and Housing      |                    |
| Housing Material            | Aluminum extruded  |
| Overall length              | 4564 mm            |
| Overall width               | 150 mm             |
| Overall height              | 43 mm              |
| Color                       | White              |

| Approval and Application               |                                    |
|--|------------------------------------|
| Ingress protection code                | IP20 [ Finger-protected]           |
| Mech. impact protection code           | IK02 [ 0.2 J standard]             |
| Surge Protection (Common/Differential) | 2.5 kV                             |
| Initial Performance (IEC Compliant)    |                                    |
| Init. Corr. Color Temperature          | 6500 K                             |
| Init. Color Rendering Index            | >80                                |
| Initial input power                    | 76 W                               |
| Power consumption tolerance            | +/-10%                             |
| Over Time Performance (IEC Compliant)  |                                    |
| Median useful life L70B50              | 50000 h                            |
| Application Conditions                 |                                    |
| Ambient temperature range              | 0 to +45 °C                        |
| Product Data                           |                                    |
| Order product name                     | SP680X2 LED78S 6500 PSD WH L240 S1 |
| Order code                             | 919515811534                       |
| Numerator - Quantity Per Pack          | 1                                  |
| Numerator - Packs per outer box        | 1                                  |
| Material Nr. (12NC)                    | 919515811534                       |

# Pureline SP680P

Net Weight (Piece) 4.990 kg




## Warnings and Safety

- Meant for use in Indoor environment only

## Dimensional drawing

Product: Pureline Suspended  
Type: SP680  
Application: Indoor



IN9002SUS - Suspended luminaires

