



# Smartbright BN100 Batten

## BN100C LED40S-4000 PSU L120 GR

High performance LED batten, can replace 2x40W conventional batten suitable for Classroom, hostel room, corridor, small shops, community center, club, small warehouse lighting applications.

### Warnings and Safety

- Meant for use in Indoor environment only

### Product data

General Information	
Driver included	Yes
Light source engine type	LED
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	-
Optical cover type	Polycarbonate
Luminaire light beam spread	120°
Operating and Electrical	
Input Voltage	220-240 V

Line Frequency	50 Hz
Power Consumption	41 W
Power Factor (Fraction)	1.9
Temperature	
Ambient temperature range	0 to +45 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Aluminum and gray
Mounting device	Click Fix Mounting bracket (Surface & Suspended)
Overall length	1,127 mm

Smartbright BN100 Batten

Overall width	40 mm
Overall height	46 mm
Dimensions (Height x Width x Depth)	46 x 40 x 1127 mm
Material	Aluminum

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Power consumption tolerance	+/-10%
-----------------------------	--------

Over Time Performance (IEC Compliant)


Median useful life L70B50	30,000 hour(s)
---------------------------	----------------

Product Data

Order product name	BN100C LED40S-4000 PSU L120 GR
Full product name	BN100C LED40S-4000 PSU L120 GR
Order code	919515811981
Material Nr. (12NC)	919515811981
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

Dimensional drawing

Dimensions



Type	Dimensions (mm)		
	L	W	H
~4ft	1127	40	46

Product: GreenBay
Type: BY400V
Application: Indoor

