



Smartbright WT200/201 waterproof

WT201C LED40S-6500 PSU L120

Smartbright Waterproof luminaire is a special application luminaire designed to provide uninterrupted lighting for dusty and humid indoor application. It is a perfect solution for lighting up indoor spaces like multilevel car park, open canopies in bus stations and general industrial applications. The luminaire has all-weather polycarbonate housing and highly efficient electronics with LED system to offer long useful life even in adverse application and environmental conditions. With unique design, variety of options in lumen packs and color temperature makes it suitable for diverse applications.

Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor exposed to Sun and Rain.

Product data

| | | | | |
|------------------------------------|-------------------|-------------------------|---------------|-----|
| Light Technical | | Power Factor (Fraction) | | 0.9 |
| Correlated Color Temperature (Nom) | 6500 K | Temperature | | |
| Color rendering index (CRI) | >80 | | | |
| Light source color | 865 cool daylight | | | |
| Luminaire light beam spread | - | | | |
| Operating and Electrical | | Controls and Dimming | | |
| Input Voltage | 220-240 V | Dimmable | No | |
| Line Frequency | 50 Hz | Control interface | - | |
| Power Consumption | 40 W | Mechanical and Housing | | |
| | | Housing Material | Polycarbonate | |

Smartbright WT200/201 waterproof

| | |
|-------------------------------------|-------------------|
| Housing Color | Gray |
| Overall length | 1,179 mm |
| Overall width | 52.3 mm |
| Overall height | 72 mm |
| Dimensions (Height x Width x Depth) | 72 x 52 x 1179 mm |
| Material | Polycarbonate |


Approval and Application

| | |
|--|--|
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK06 [1 J] |
| Surge Protection (Common/Differential) | 2.5 kV |
| Protection class IEC | Safety class I |

| Initial Performance (IEC Compliant) | |
|-------------------------------------|-----------------------------|
| Power consumption tolerance | +/-10% |
| Product Data | |
| Order product name | WT201C LED40S-6500 PSU L120 |
| Full product name | WT201C LED40S-6500 PSU L120 |
| Order code | 919515811997 |
| Material Nr. (12NC) | 919515811997 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 6 |

Dimensional drawing


Product: SmartBright
Type: WT201C & WT200C
Application: Indoor Industrial



Product

WT201C LED40S-6500 PSU L120

Product: GreenBay
Type: BY400V
Application: Indoor



Product: SmartBright
Type: WT201C & WT200C
Application: Indoor Industrial

