



# Smartbright WT200/201 waterproof

## WT201C LED40S-6500 PSU L120

Smartbright Waterproof luminaire is a special application luminaire designed to provide uninterrupted lighting for dusty and humid indoor application. It is a perfect solution for lighting up indoor spaces like multilevel car park, open canopies in bus stations and general industrial applications. The luminaire has all-weather polycarbonate housing and highly efficient electronics with LED system to offer long useful life even in adverse application and environmental conditions. With unique design, variety of options in lumen packs and color temperature makes it suitable for diverse applications.

### Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor exposed to Sun and Rain.

### Product data

Light Technical		Power Factor (Fraction)		0.9
Correlated Color Temperature (Nom)	6500 K			
Color rendering index (CRI)	>80	Temperature		
Light source color	865 cool daylight	Ambient temperature range		0 to +45 °C
Luminaire light beam spread	-			
Operating and Electrical		Controls and Dimming		
Input Voltage	220-240 V	Dimmable		No
Line Frequency	50 Hz	Control interface		-
Power Consumption	40 W	Mechanical and Housing		
		Housing Material		Polycarbonate

Smartbright WT200/201 waterproof

Housing Color	Gray
Overall length	1,179 mm
Overall width	52.3 mm
Overall height	72 mm
Dimensions (Height x Width x Depth)	72 x 52 x 1179 mm
Material	Polycarbonate

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)


Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	WT201C LED40S-6500 PSU L120
Full product name	WT201C LED40S-6500 PSU L120
Order code	919515811997
Material Nr. (12NC)	919515811997
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

Dimensional drawing


Product: SmartBright  
Type: WT201C & WT200C  
Application: Indoor Industrial



Product

WT201C LED40S-6500 PSU L120

Product: GreenBay  
Type: BY400V  
Application: Indoor



Product: SmartBright  
Type: WT201C & WT200C  
Application: Indoor Industrial

