



Smartbright WT200/201 waterproof

WT201C LED40S-4000 PSU L120

Smartbright Waterproof luminaire is a special application luminaire designed to provide uninterrupted lighting for dusty and humid indoor application. It is a perfect solution for lighting up indoor spaces like multilevel car park, open canopies in bus stations and general industrial applications. The luminaire has all-weather polycarbonate housing and highly efficient electronics with LED system to offer long useful life even in adverse application and environmental conditions. With unique design, variety of options in lumen packs and color temperature makes it suitable for diverse applications.

Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor exposed to Sun and Rain.

Product data

Light Technical	
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80
Light source color	840 neutral white
Luminaire light beam spread	-

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 Hz
Power Consumption	41 W

Power Factor (Fraction)	1.9
-------------------------	-----

Temperature	
Ambient temperature range	0 to +45 °C

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Polycarbonate

Smartbright WT200/201 waterproof

Housing Color	Gray
Overall length	1,179 mm
Overall width	52.3 mm
Overall height	72 mm
Dimensions (Height x Width x Depth)	72 x 52 x 1179 mm
Material	Polycarbonate


Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Power consumption tolerance	+/-10%
Product Data	
Order product name	WT201C LED40S-4000 PSU L120
Full product name	WT201C LED40S-4000 PSU L120
Order code	919515811998
Material Nr. (12NC)	919515811998
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

Dimensional drawing


Product: SmartBright
Type: WT201C & WT200C
Application: Indoor Industrial



Product

WT201C LED40S-4000 PSU L120

Product: GreenBay
Type: BY400V
Application: Indoor



Product: SmartBright
Type: WT201C & WT200C
Application: Indoor Industrial

