



# Standard Extra Low Voltage A60

## STAN ELV 40W E27/BRC 24V A60 CL 1CT

Clear lamp (A-bulb) for operation on voltages of 24 and 50V

### Product data


General Information	
Cap base	E27 [ E27]
Operating position	UNIVERSAL [ Any/Universal]
Nominal lifetime (nom.)	1000 h
Switching cycle	4000X
Light Technical	
Luminous flux (nom.)	580 lm
Luminous flux (rated) (nom.)	580 lm
Correlated colour temperature (nom.)	2700 K
Color rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	40 W
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Voltage (Nom)	24 V
Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Clear (CL)
Cap base information	Brass [ Brass Cap]
Approval and Application	
Energy efficiency label (EEL)	D
Energy Consumption kWh/1000 h	40 kWh

Product Data	
Full product code	871150002293684
Order product name	Standard ELV 40W E27/BRC 24V A60 CL 1CT
EAN/UPC – product	8711500022936
Order code	02293684
Local Code	2440ESCP
Numerator – quantity per pack	1
Numerator – packs per outer box	120
Material no. (12NC)	920011020503
Net weight (piece)	28.000 g
ILCOS Code	IAA/C-40-24-E27-60

## Standard Extra Low Voltage A60

### Dimensional drawing



Product	D (max)	C (max)
Standard ELV 40W E27/BRC 24V A60 CL 1CT	60 mm	107.5 mm

ELV 40W E27/BRC 24V A60 CL

