



Standard Extra Low Voltage A60

STAN ELV 60W E27/BRC 24V A60 CL 1CT/20

Clear lamp (A-bulb) for operation on voltages of 12, 24, 42 and 50 V

Product data

General Information	
Cap base	E27 [E27]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime (nom.)	1000 h
Switching cycle	4,000X
Rated lifetime (hours)	1000 h

Light Technical	
Luminous flux (nom.)	970 lm
Luminous flux (rated) (nom.)	970 lm
Correlated Colour Temperature (Nom)	2700 K
Colour rendering index (nom.)	100

Operating and Electrical	
Power (Rated) (Nom)	60.0 W
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Voltage (Nom)	24 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Cap-base information	Brass [Brass Cap]
Bulb shape	A60 [A 60mm]

Approval and Application	
Energy consumption kWh/1,000 hours	60 kWh

Product Data	
Full product code	871150009018805
Order product name	Standard ELV 60W E27/BRC 24V A60 CL 1CT/20
EAN/UPC – product	8711500090188
Order code	09018805
SAP numerator – quantity per pack	1
Numerator – packs per outer box	20
SAP material	920021020517
SAP net weight (piece)	28.000 g
ILCOS code	IAA/C-60-24-E27-60

Standard Extra Low Voltage A60

Dimensional drawing

Product	D (max)	C (max)
Standard ELV 60W E27/BRC 24V A60 CL 1CT/20	60 mm	107.5 mm

ELV 60W E27/BRC 24V A60 CL

