



Standard Extra Low Voltage A60

STAN ELV 60W E27/BRC 24V A60 CL 1CT/20

Clear lamp (A-bulb) for operation on voltages of 12, 24, and 42V

Product data


General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal Lifetime (Nom)	1000 h
Switching Cycle	4000X
Light Technical	
Luminous Flux (Nom)	970 lm
Luminous Flux (Rated) (Nom)	970 lm
Colour Temperature, horizontal (Nom)	2700 K
Colour Rendering Index horiz (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	60.0 W
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Voltage (Nom)	24 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear (CL)
Cap-Base Information	Brass [Brass Cap]
Approval and Application	
Energy Efficiency Label	D
Energy Consumption kWh/1000 h	60 kWh

Product Data	
Full product code	871150009018805
Order product name	Standard ELV 60W E27/BRC 24V A60 CL 1CT/20
EAN/UPC - Product	8711500090188
Order code	09018805
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	920021020517
Net Weight (Piece)	28.000 g
ILCOS Code	IAA/C-60-24-E27-60

Standard Extra Low Voltage A60

Dimensional drawing



Product	D (max)	C (max)
Standard ELV 60W E27/BRC 24V A60 CL 1CT/20	60 mm	107.5 mm

ELV 60W E27/BRC 24V A60 CL

