



Standard Life PS

300M 120/130V 12/1PK

Standard Life Incandescent, vacuum or gas-filled lamp has a crystal clear bulb and a completely visible filament, so the brightness of the light is not 'softened.' It imparts a sparkling radiance to larger luminaires and wall brackets with textured or satin-etched glass and cut crystal. It is the appropriate lamp for large luminaires with clear glass bowls, mounted indoors or outdoors. It is recommended in all such cases where brilliance and sparkle are more important than the avoidance of glare. These lamps are also used for indirect lighting in closed luminaires.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	750 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux (Max)	4,625 lm
Luminous Flux	6,280 lm
Operating and Electrical	
Power Consumption	300 W
Voltage (Nom)	120-130 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	PS25
Product Data	
Order product name	300M 120/130V 12/1PK
Full product name	300M 120/130V 12/1PK
Order code	133918
Material Nr. (12NC)	920140734302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677133917
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677133912

Standard Life PS

Dimensional drawing



Product
300M 120/130V 12/1PK

