



Rough / Vibration Service

100A/RS 250V 60PK

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.


Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Industrial Rough Service (RS)
Gas Filling	GAS
Light Technical	
Initial lumen (Nom)	1030 lm
Operating and Electrical	
Power (Rated) (Nom)	100 W
Voltage (Nom)	250 V
Mechanical and Housing	
Bulb Finish	Frosted

Filament Shape	C-9 [Pendant]
Product Data	
XUCDM.COPY.Product.Title	100A/RS 250V 60PK
EAN/UPC - Product	046677275501
Order code	275503
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	60
Material Nr. (12NC)	920647046205
Net Weight (Piece)	0.001 kg

Rough / Vibration Service

Dimensional drawing



A21

100W E26 250V A21 FR

Product	D	C (max)
100A/RS 250V 60PK	2.625 in	5.312 in

