



DuraMax Reflector Flood

65BR/FL60/LL 120V 4/2 TP

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.


Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Base Up Horizontal (BUH) [Base Up Horizontal (BUH)]
Main Application	Flood and Ambient Lighting
Gas Filling	GAS
Life with 3 Hour Per Day Use	2.3 a
Footnote Incandescent 1	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)
Light Technical	
Beam Angle (Nom)	60 °
Initial lumen (Nom)	625 lm
Beam Description	Flood [Flood]
Correlated Color Temperature (Nom)	2740 K

Operating and Electrical	
Power (Rated) (Nom)	65 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Frosted
Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	CC6 [Straight]
Approval and Application	
Estimated Energy Cost Per Year	7.83 \$
Product Data	
Order product name	65BR/FL60/LL 120V 4/2 TP
EAN/UPC - Product	50046677139273
Order code	139279
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	920670136320
Net Weight (Piece)	0.001 kg

DuraMax Reflector Flood

Dimensional drawing



65W E26 120V BR40 FL FR

Product

65BR/FL60/LL 120V 4/2 TP

