



# Reflector Flood

## 65BR/FL60 130V CDA 24/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	60 degree(s)
Luminous Flux	565 lm
Operating and Electrical	
Power Consumption	65 W
Voltage (Nom)	130 V
Voltage (Nom)	130 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BR40
Product Data	
Order product name	65BR/FL60 130V CDA 24/1
Full product name	65BR/FL60 130V CDA 24/1
Order code	225375
Material Nr. (12NC)	920670336103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677225377
Numerator - Packs per outer box	24
EAN/UPC - Case	50046677225372

## Reflector Flood

### Dimensional drawing



#### Product

65BR/FL60 130V CDA 24/1

