



# Reflector Flood

## 300BR/FL 120/130V 24/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	55 degree(s)
Luminous Flux	2,480 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	300 W
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BR40
Approval and Application	
Approval Marks	Circle E logo
Product Data	
Order product name	300BR/FL 120/130V 24/1
Full product name	300BR/FL 120/130V 24/1
Order code	920673035502
Material Nr. (12NC)	920673035502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677143435
Numerator - Packs per outer box	24
EAN/UPC - Case	50046677143430

## Reflector Flood

### Dimensional drawing



#### Product

300BR/FL 120/130V 24/1

