



# Reflector Flood

## 65BR30/FLVALUE PACK 1/12

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Universal [ Universal]
Main Application	Indoor Reflector
Gas Filling	GAS
Life with 3 Hour Per Day Use	1.8 a
Footnote Incandescent 1	Consider the compact fluorescent lamps for energy savings.
Footnote Incandescent 2	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)
Light Technical	
Beam Angle (Nom)	55 °
Initial lumen (Nom)	620 lm
Beam Description	Flood [ Flood]
Correlated Color Temperature (Nom)	2710 K
Operating and Electrical	
Power (Rated) (Nom)	65 W

Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Frosted (FR)
Cap-Base Information	Aluminium [ Aluminium Cap]
Filament Shape	CC6 [ Straight]
Approval and Application	
Estimated Energy Cost Per Year	7.83 \$
Product Data	
Order product name	65BR30/FLVALUE PACK 1/12
EAN/UPC - Product	50046677225822
Order code	248872
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	920681036368
Net Weight (Piece)	0.052 kg

# Reflector Flood

## Dimensional drawing



### Product

65BR30/FLVALUE PACK 1/12

65W E26 120V BR30 FL FR

