



Reflector BR38 Flood

75BR30/PK CDA 120V 8/1


Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These reflector lamps come in multiple colors ideal for holiday, party or special effects lighting.

Product data

General Information		Mechanical and Housing	
Cap-Base	E26 [Single Contact Medium Screw]	Bulb Finish	Pink
Operating Position	UNIVERSAL [Any or Universal (U)]	Bulb Shape	BR30
Nominal lifetime	2,000 hour(s)		
Rated Lifetime (Hours)	2,000 hour(s)		
Lighting Technology	Incandescent		
Light Technical		Approval and Application	
Beam Angle (Nom)	55 degree(s)	Approval Marks	Circle E logo
Luminous Flux	555 lm		
Color rendering index (CRI)	100		
Operating and Electrical		Product Data	
Power Consumption	75 W	Order product name	75BR30/PK CDA 120V 8/1
Warm-up time to 60% light	instant full light s	Full product name	75BR30/PK CDA 120V 8/1
Voltage (Nom)	120 V	Order code	249029
Voltage (Nom)	120 V	Material Nr. (12NC)	920681336304
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	046677227395
		Numerator - Packs per outer box	8
		EAN/UPC - Case	50046677227390

Reflector BR38 Flood

Dimensional drawing



Product

75BR30/PK CDA 120V 8/1

