



# Reflector BR38 Flood

75BR30/PK CDA 120V 8/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These reflector lamps come in multiple colors ideal for holiday, party or special effects lighting.


## Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	55 degree(s)
Luminous Flux	555 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	75 W
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Pink
Bulb Shape	BR30
Approval and Application	
Approval Marks	Circle E logo
Product Data	
Order product name	75BR30/PK CDA 120V 8/1
Full product name	75BR30/PK CDA 120V 8/1
Order code	920681336304
Material Nr. (12NC)	920681336304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677227395
Numerator - Packs per outer box	8
EAN/UPC - Case	50046677227390

# Reflector BR38 Flood

## Dimensional drawing



Product
75BR30/PK CDA 120V 8/1

