



DuraMax Reflector Flood

65BR30/FL55/LL TP 120V 4/3

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.

Product data


General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Flood and Ambient Lighting
Gas Filling	GAS
Life with 3 Hour Per Day Use	2.3 a
Footnote Incandescent 1	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)
Rated Lifetime (Hours)	2500 h
Light Technical	
Beam Angle (Nom)	55 °
Initial lumen (Max)	620 lm
Initial lumen (Nom)	610 lm
Beam Description	Flood [Flood]

Correlated Color Temperature (Max) 2710 K	
Operating and Electrical	
Power (Rated) (Nom)	65 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Frosted
Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	CC6 [Straight]
Bulb Shape	BR30 [BR30 (BR30)]
Approval and Application	
Estimated Energy Cost Per Year	7.83 \$
Product Data	
Order product name	65BR30/FL55/LL TP 120V 4/3
EAN/UPC - Product	50046677223040
Order code	223040
Numerator - Quantity Per Pack	1

DuraMax Reflector Flood

Numerator - Packs per outer box	4
Material Nr. (12NC)	920681636371
Net Weight (Piece)	0.000 kg

Dimensional drawing



65W E26 120V BR30 FL FR

Product

65BR30/FL55/LL TP 120V 4/3

