



# DuraMax Reflector Spot

## 65BR30/SP20/LL 120V 12/1 TP

Philips DuraMax® Long Life Light Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. A wide assortment of shapes, sizes and wattages ensure that there is a DuraMax product to meet most basic lighting needs.

### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Base Up Horizontal (BUH) [ Base Up Horizontal (BUH)]
Main Application	Indoor Reflector
Gas Filling	GAS
Life with 3 Hour Per Day Use	2.3 a
Footnote Incandescent 1	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)

Light Technical	
Beam Angle (Nom)	20 °
Initial lumen (Nom)	620 lm
Beam Description	Spot
Correlated Color Temperature (Nom)	2710 K

Operating and Electrical	
Power (Rated) (Nom)	65 W
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear (CL)
Cap-Base Information	Aluminium [ Aluminium Cap]
Filament Shape	CC6 [ Straight]

Approval and Application	
Estimated Energy Cost Per Year	7.83 \$


  

Product Data	
Order product name	65BR30/SP20/LL 120V 12/1 TP
EAN/UPC - Product	046677167691
Order code	167692
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	920681836309
Net Weight (Piece)	0.066 kg

## DuraMax Reflector Spot

---

### Dimensional drawing



#### Product

65BR30/SP20/LL 120V 12/1 TP

65W E26 120V BR30 SP CL

